



YDS30LT, Full Tension Splice

By Burndy
Catalog # [YDS30LT](#)



Full Tension Splice, 312.8 kcmil 6201, 317 Index

Features

- Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	266.8
Conductor - ACSR Cmpt Size	266.8
Conductor - AAAC 5005 Size Range	312.8 kcmil
Conductor - AAAC 6201 Size Range	312.8
Conductor - AAAC 6201 Size	312.8
Conductor - AL Str Size	266.8
Conductor - AAAC 5005 Size	312.8
Conductor - AL Str Size Range	266.8
Conductor Type	- ACSR C Str-Size - AL C Str-Size 266.8 (26/7) Owl 266.8 (26/7) Partridge
Conductor - ACSR Str Size	
Conductor - ACSR Str Size Range	266.8 (26/7) Owl-266.8 (26/7) Partridge

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	7-3/20 in
Dimension - L Length Overall	366 mm
	mm
Dimension - B Length inch	7.15 in
Dimension - Length Overall	14.42 in
	inch

General

Plated	N
Trade Name	UNISPLICE™
Die Index	317
UPC	781810014950
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810014950
UPC 14 Digit GTIN	00781810014950

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)