



YDS30R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS30R](#)

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, Inner Sleeve: 6.00 IN L, Outer Sleeve: 19.75 IN L

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	266.8
Conductor - ACSR Cmpt Size	266.8
Conductor - AL Str Size	266.8
Conductor - AL Str Size Range	266.8
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	• 266.8 (26/7) Owl • 266.8 (26/7) Partridge
Conductor - ACSR Str Size Range	266.8 (26/7) Owl-266.8 (26/7) Partridge

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Aluminum Sleeve Length inch	19.75
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	502
Dimension - Steel Sleeve Length inch	6
Dimension - Length Overall inch	19.75

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 250 • 251
Die Index - Element A	250
Die Index - Element B	251
UPC	781810015629
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015629
UPC 14 Digit GTIN	00781810015629

Logistics

Minimum Pack Quantity	20
Pallet Quantity	1920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)