



YDS311AT, Aluminum Full Tension Sleeve

By Burndy
Catalog # [YDS311AT](#)



Al Full Tension Sleeve Splice, 397.5 kcmil(Al), 12.22" L, 468 Index

Features

- Full-Tension sleeve made of aluminum tubing with staked-in cable stop
- Sizes 1/0 and larger feature a taper for gradual transition of stress
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	397.5(19)kcmil
Conductor - AL Str Size Range	397.5
Conductor - ACSR Str Size	397.5 (18/1) Chickadee
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	310 mm
Dimension - Outside Diameter	1.19 in
Dimension - B Length fraction	6-1/20 in
Dimension - B Length inch	6.05 in
Dimension - Length Overall	12.22 in

General

Trade Name	HYSPLICE™
Die Index	468
Prefilled Oxide Inhibitor	Y
Insulation	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810015933
Type	YDS-AT
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015933
UPC 14 Digit GTIN	00781810015933

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1680
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)