

YDS312E, Full Tension Steel Splice

By Burndy
Catalog # [YDS312E](#)

Full-tension steel splice designed for galvanized steel guy, messenger and "static:" conductors. ANSI C119.4 Class 1 (Full Tension),Die index:305

Features

- Full Tension Steel Splice
- Designed for Galvanized Steel Guy, Messenger and "Static" Conductors

Specifications


Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Grade	EHS
Conductor - Galvanized Steel Str Size	5/16 (7) in
Conductor - Galvanized Steel Str Size Range	5/16 (7) in
Conductor - AL Coated Steel Size Range	5/16 (7) in
Conductor - AL Coated Steel Size	5/16 (7) in
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------



Dimensions

Dimension - B Length fraction	4-17/81 in
Dimension - L Length Overall mm	214 mm
Dimension - B Length inch	3.89 inch
Dimension - Outside Diameter inch	0.71 in
Dimension - Inside Diameter inch	0.36 in
Dimension - Length Overall inch	8.41 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	305
UPC	781810015919
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015919
UPC 14 Digit GTIN	00781810015919

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1170
Carton Quantity	13

Product Assets

[Catalog \[English\]](#)