



YDS312H, Full Tension Steel Splice

By Burndy
Catalog # [YDS312H](#)

Full-tension steel splice designed for galvanized steel guy, messenger and "static:" conductors. ANSI C119.4 Class 1 (Full Tension),Die index:257

Features

- Full Tension Steel Splice
- Designed for Galvanized Steel Guy, Messenger and "Static" Conductors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No


Conductor

Conductor - Grade	HS
Conductor - Galvanized Steel Str Size	5/16 (7) in
Conductor - Galvanized Steel Str Size Range	5/16 (7) in
Conductor - AL Coated Steel Size Range	5/16 (7) in
Conductor - AL Coated Steel Size	5/16 (7) in
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions



Package Height	0.000 in
Dimension - B Length fraction	5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	268 mm
Dimension - B Length inch	5 in
Dimension - Outside Diameter inch	0.66 in
Dimension - Length Overall inch	10.55 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	257
UPC	781810015926
Prefilled Oxide Inhibitor	Y
Material	Steel
Plating Type	Unplated
UPC 12 Digit	781810015926
UPC 14 Digit GTIN	00781810015926

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2184
Carton Quantity	13

Product Assets

[Catalog \[English\]](#)