



YDS32, Copper Full Tension Splice

By Burndy
Catalog # [YDS32](#)



CU Full Tension Splice, Accommodates Wire: 400 kcmil Cu (Hard, Medium, or Soft Drawn), Die Index: 209

Features

- Copper Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	400 kcmil
-----------------------------	-----------

Configuration

Physical Attribute - Number of	5
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	6-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	326 mm
Dimension - B Length inch	6.25 in
Dimension - Outside Diameter	1.24 in
Dimension - Length Overall	12.83 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	209
Oxide Inhibitor Type	Penetrox E
UPC	781810014660
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014660

Logistics

Minimum Pack Quantity	1
Pallet Quantity	702
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)