



YDS321R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS321R](#)

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, Inner Sleeve: 4.75 IN L, Outer Sleeve: 17.88 IN L

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	336.4 kcmil
Conductor - ACSR Cmpt Size	336.4 kcmil
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	336.4 (18/1) Merlin kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	17.875 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	121 mm
Dimension - Steel Sleeve Length inch	4.75 in
Dimension - Length Overall inch	4.75 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 242 • 490
Die Index - Element A	242
Die Index - Element B	490
UPC	781810821053
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810821053
UPC 14 Digit GTIN	00781810821053

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)



A Hubbell brand