



YDS326R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS326R](#)

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, Inner Sleeve: 6.25 IN L, Outer Sleeve: 26.38 IN L

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	477.0 (24/7) Flicker
Conductor - ACSR Str Size Range	477.0 (24/7) Flicker

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	26.375 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in



Dimension - L Length Overall mm	672 mm
Dimension - Outside Diameter inch	1.36 in
Dimension - Steel Sleeve Length inch	6.25 in
Dimension - Length Overall inch	26.44 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 253 • 261
Die Index - Element A	253
Die Index - Element B	261
UPC	781810015964
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015964
UPC 14 Digit GTIN	00781810015964

Logistics

Minimum Pack Quantity	1
Pallet Quantity	350
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand