



YDS32LT, Full Tension Splice

By Burndy
Catalog # [YDS32LT](#)

Full Tension Splice, 394.5 kcmil 6201, 394.5 kcmil 5005 (336.4 E.C. Equiv.), 642 Index



Features

- Eliminates strand stripping, installing separate steel sleeve and filling with joint compound

Application

Pre-filled with PENETROX joint compound, stripsealed and capped to limit oxide growth and to increase the life of the connection

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	394.5 kcmil
Conductor - AAAC 6201 Size Range	394.5
Conductor - AAAC 6201 Size	394.5
Conductor - AAAC 5005 Size	394.5
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	432 mm
Dimension - Outside Diameter	1.38 in
Dimension - Inside Diameter	0.78 in
Dimension - Length Overall	17 in

General

Plated	N
Trade Name	UNISPLICE™
Sub Brand	UNISPLICE
Die Index	642
UPC	781810015667
Type	YDS-LT
Prefilled Oxide Inhibitor	Y
Construction Material - Main	Aluminum
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015667
UPC 14 Digit GTIN	00781810015667

Logistics

Minimum Pack Quantity	1
Pallet Quantity	960
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)