



YDS32R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS32R](#)



2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, Inner Sleeve: 6.88 IN L, Outer Sleeve: 22.25 IN L

Features

- 2-Piece, Full Tension HYSPLICE consists of aluminum outer sleeve and steel inner sleeve
- Tapered out sleeve provides gradual transition of stress
- Filler hole provided for PENETROX Joint Compound
- Sizes 1/O and larger come supplied with plugs for filler hole

Application

For ACSR, Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	336.4 kcmil
Conductor - ACSR Cmpt Size	336.4 kcmil
Conductor - ACSR Str Size	• 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet kcmil-336.4 (30/7) Oriole kcmil
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	565 mm
Dimension - Steel Sleeve Length inch	6.875 in
Dimension - Aluminum Sleeve Length inch	22.25 in
Dimension - Length Overall inch	22.25 in

General

Trade Name	HYSPLICE™
Die Index	• 252 • 316
Die Index - Element A	252
Die Index - Element B	316
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810821022
Type	YDS-R Set
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810821022
UPC 14 Digit GTIN	00781810821022

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand