



YDS33R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS33R](#)

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, Inner Sleeve: 8.63 IN L, Outer Sleeve: 22.25 IN L

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	336.4 kcmil
Conductor - ACSR Cmpt Size	336.4 kcmil
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	336.4 (30/7) Oriole kcmil
Conductor - ACSR Str Size Range	336.4 (30/7) Oriole kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	22.25 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	219 mm
Dimension - Steel Sleeve Length inch	8.625 in
Dimension - Length Overall inch	8.63 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 305 • 316
Die Index - Element A	305
Die Index - Element B	316
UPC	781810015681
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015681
UPC 14 Digit GTIN	00781810015681

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand