



YDS341RL, Full Tension Splice

By Burndy
Catalog # [YDS341RL](#)

Full Tension Splice, 397.5 kcmil ACSR (18-1) 419.6 kcmil 5005, 327
Index

Features

- Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	465.4 (19) kcmil
Conductor - AAAC 6201 Size Range	465.4 (19) kcmil
Conductor - AAAC 6201 Size	465.4 (19) kcmil
Conductor - AAAC 5005 Size	465.4 (19) kcmil
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	10-9/10 in
Dimension - L Length Overall mm	557 mm
Dimension - B Length inch	10.9 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Length Overall inch	21.92 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	327
UPC	781810821268
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810821268
UPC 14 Digit GTIN	00781810821268

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)