



YDS34R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS34R](#)

2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, Inner Sleeve: 6.25 IN L, Outer Sleeve: 25.63 IN L

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	• 397.5 (26/7) Ibis • 397.5 (30/7) Lark
Conductor - ACSR Str Size Range	397.5 (26/7) Ibis-397.5 (30/7) Lark

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	25.625 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	650 mm
Dimension - Outside Diameter inch	1.25 in
Dimension - Steel Sleeve Length inch	6.25 in
Dimension - Length Overall inch	25.59 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 253 • 317
Die Index - Element A	253
Die Index - Element B	317
UPC	781810015704
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015704
UPC 14 Digit GTIN	00781810015704

Logistics

Minimum Pack Quantity	1
Pallet Quantity	600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand