



YDS351AT, Alluminum, Full Tension Sleeve

By Burndy
Catalog # [YDS351AT](#)



HYSPLICE™, 556.5 (19, 37) kcmil, 12-3/4 in L, Full Tension Sleeve
for All Aluminum Compressed and Compact Conductors

Features

- Full-Tension sleeve made of aluminum tubing with staked-in cable stop
- Sizes 1/0 and larger feature a taper for gradual transition of stress
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	556.5
Conductor - AL Str Size Range	556.5
Conductor Type	AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	651 mm
Dimension - Outside Diameter	1.39 in
Dimension - B Length fraction	6-3/10 in
Dimension - B Length inch	6.3 in
Dimension - Length Overall	25.63 in
inch	

General

Trade Name	HYSPLICE™
Die Index	261
Prefilled Oxide Inhibitor	Y
Insulation	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810015988
Type	YDS-AT
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015988
UPC 14 Digit GTIN	00781810015988

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)