



YDS361AT, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy
Catalog # [YDS361AT](#)

Full tension splice made of aluminum tubing with staked -in cable stop. Designed for all aluminum conductor. ANSI C119.4 Class 1 (Full Tension)

Features

- Aluminum Full Tension Splice
- Staked in Cable Stop

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	636(37)kcmil
Conductor - AL Str Size Range	636 kcmil
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	636 (30/19) Egret kcmil
Conductor - ACSR Str Size Range	636 (30/19) Egret kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	6-2/3 in
Package Weight	0.000 lb.



Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	342 mm
Dimension - B Length inch	6.67 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Length Overall inch	13.47 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	469
UPC	781810085134
Prefilled Oxide Inhibitor	Y
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810085134
UPC 14 Digit GTIN	00781810085134

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1638
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)