



YDS361RLY, 1-piece Aluminum Full Tension Splice

By Burndy
Catalog # [YDS361RLY](#)

One piece full tension aluminum splice designed to eliminate possible basketing of conductor. Installed by crimping from end of connector towards the center.

Features

- Aluminum 1-piece Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	477(18-1)kcmil
Conductor - AL Str Size Range	477 kcmil
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	12-11/25 in
-------------------------------	-------------

Dimension - L Length Overall mm	635 mm
Dimension - B Length inch	12.44 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Length Overall inch	25 in

General

Plated	N
Die Index	788 720
UPC	781810042267
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810042267
UPC 14 Digit GTIN	00781810042267

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)