



YDS36LT, Full Tension Splice

By Burndy
Catalog # [YDS36LT](#)

Full Tension Splice, 559.5 kcmil 6201, 559.5 kcmil 5005 (477 E.C. Equiv.), 667 Index



Features

- Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	559.5 (19) kcmil
Conductor - AAAC 6201 Size Range	559.5 (19) kcmil
Conductor - AAAC 6201 Size	559.5 (19) kcmil
Conductor - AAAC 5005 Size	559.5 (19) kcmil
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	477.0 (26/7) Hawk kcmil
Conductor - ACSR Str Size Range	477.0 (26/7) Hawk kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	406 mm
Dimension - Length Overall	16 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	667
UPC	781810015742
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810015742
UPC 14 Digit GTIN	00781810015742

Logistics

Minimum Pack Quantity	1
Pallet Quantity	960
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)