



YDS39, Copper, Single Sleeve Full Tension Splice



By Burndy
Catalog # [YDS39](#)

CU Full Tension Splice, Accommodates Wire: 750 kcmil Cu (Hard, Medium, or Soft Drawn), Die Index: 627

Features

- Single Sleeve, Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	750 kcmil
-----------------------------	-----------

Configuration

Physical Attribute - Number of Crimps Required	7
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	6-1/100in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	325 mm
Dimension - B Length inch	6.01 in
Dimension - Outside Diameter inch	1.70 in
Dimension - Length Overall inch	12.78 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	627
Oxide Inhibitor Type	Penetrox E
UPC	781810821121
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810821121

Logistics

Minimum Pack Quantity	1
Pallet Quantity	234
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)