



YDS391AT, Aluminum, Full Tension Sleeve

By Burndy
Catalog # [YDS391AT](#)



HYSPLICE™, 13-5/8 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors

Features

- Full-Tension sleeve made of aluminum tubing with staked-in cable stop
- Sizes 1/0 and larger feature a taper for gradual transition of stress
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	800 kcmil
Conductor - AL Str Size Range	800 kcmil
Conductor - ACSR Str Size	795 (30/19) Mallard kcmil
Conductor - ACSR Str Size Range	795 (30/19) Mallard kcmil
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	344 mm
Dimension - Outside Diameter	1.67 in
Dimension - B Length fraction	6-18/25 in
Dimension - B Length inch	6.72 in
Dimension - Length Overall	13.56 in

General

Trade Name	HYSPLICE™
Die Index	342
Prefilled Oxide Inhibitor	Y
Insulation	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810821169
Type	YDS-AT
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810821169
UPC 14 Digit GTIN	00781810821169

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)