



YDS391RLG2, Aluminum, Full Tension Splice

By Burndy
Catalog # [YDS391RLG2](#)

Al Compression Full Tension Splice, 556.5 Kcmil ACSR

Features

- Aluminum Full Tension Sleeve

Specifications

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	556.5
Conductor - AL Str Size Range	556.5
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	447.0 (26/7) Hawk
Conductor - ACSR Str Size Range	447.0 (26/7) Hawk

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	7-23/25 in
Dimension - L Length Overall mm	413 mm
Dimension - B Length inch	7.74 inch

Dimension - Outside Diameter inch	1.41 in
Dimension - Inside Diameter inch	0.93 in
Dimension - Length Overall inch	16.27 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	318
UPC	781810179314
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810179314
UPC 14 Digit GTIN	00781810179314

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1152
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)