



YDS392R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS392R](#)

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	• 556.5 (24/7) Parakeet • 556.5 (26/7) Dove
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet-556.5 (26/7) Dove

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - Aluminum Sleeve Length inch	26.125 in
Dimension - L Length Overall mm	664 mm

Dimension - Outside Diameter inch	1.5 in
Dimension - Steel Sleeve Length inch	8.625 in
Dimension - Length Overall inch	26.13 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 305 • 608
Die Index - Element A	305
Die Index - Element B	608
UPC	781810109007
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810109007
UPC 14 Digit GTIN	00781810109007

Logistics

Minimum Pack Quantity	10
Pallet Quantity	350
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand