



YDS3C3, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS3C3](#)

CU Full Tension Splice, Accommodates Wire: #3 (3) Cu STR
(Hard, Medium, or Soft Drawn), Die Index: 163

Features

- Copper Full Tension Splice
- Single Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	3 AWG
-----------------------------	-------

Configuration

Physical Attribute - Number of	3
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - L Length Overall	133 mm

Dimension - B Length inch	2.50 in
Dimension - Outside Diameter	0.50 in
inch	
Dimension - Length Overall	5.25 in
inch	

General

Plated	N
Trade Name	HYSPLICE™
Die Index	163
Oxide Inhibitor Type	Penetrox E
UPC	781810014493
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014493

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)

