



YDS3K5, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS3K5](#)



CU Full Tension Splice, Accommodates Wire: 3/8 COPPERWELD,
Die Index: 259

Features

- Copper Full Tension Splice
- Single Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str	• 3#5
Size	• 3/8 (7#8)

Configuration

Physical Attribute - Number of	2
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-3/10 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	162 mm
mm	
Dimension - B Length inch	2.30 in
Dimension - Outside Diameter	0.95 in
inch	
Dimension - Length Overall	6.36 in
inch	

General

Plated	N
Trade Name	HYSPLICE™
Die Index	259
UPC	781810014516
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014516

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1470
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)