



YDS3K6, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS3K6](#)



CU Full Tension Splice, Accommodates Wire: 11/32
COPPERWELD, Die Index: 331

Features

- Copper Full Tension Splice
- Single Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	11/32 (7#9) (3#6)
---------------------------------	-------------------

Configuration

Physical Attribute - Number of Crimps Required	3
Connector Type	Splice

Dimensions

Dimension - B Length fraction	4-13/50 in
-------------------------------	------------

Dimension - L Length Overall mm	218 mm
Dimension - B Length inch	4.26 in
Dimension - Outside Diameter inch	0.91 in
Dimension - Length Overall inch	8.58 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	331
UPC	781810014523
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014523

Logistics

Minimum Pack Quantity	15
Pallet Quantity	900
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)