



YDS3K7, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS3K7](#)

CU Full Tension Splice, Accommodates Wire: 5/16
COPPERWELD, Die Index: 167

Features

- Copper Full Tension Splice
- Single Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str	• 3#7
Size	• 5/16 (7 #10)

Configuration

Physical Attribute - Number of	5
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - B Length fraction	1-17/25 in
-------------------------------	------------

Dimension - L Length Overall	249 mm
Dimension - B Length inch	4.68 in
Dimension - Outside Diameter	0.79 in
inch	
Dimension - Length Overall	9.80 in
inch	

General

Plated	N
Trade Name	HYSPLICE™
Die Index	167
UPC	781810014530
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014530

Logistics

Minimum Pack Quantity	15
Pallet Quantity	1575
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)