



YDS3K8, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS3K8](#)



CU Full Tension Splice, Accommodates Wire: 3#8 COPPERWELD,
Die Index: 205

Features

- Copper Full Tension Splice
- Single Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	3#8
---------------------------------	-----

Configuration

Physical Attribute - Number of Crimps Required	5
Connector Type	Splice

Dimensions

Dimension - B Length fraction	1-23/50 in
-------------------------------	------------

Dimension - L Length Overall mm	133 mm
Dimension - B Length inch	2.46 in
Dimension - Outside Diameter inch	0.67 in
Dimension - Length Overall inch	5.22 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	339
UPC	781810014547
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014547

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3675
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)