



YDS3W, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS3W](#)

CU Full Tension Splice, Accommodates Wire: #3 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 163

Features

- Copper Full Tension Splice
- Single Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	3 AWG
-------------------------------	-------

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-21/100 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in



Dimension - L Length Overall mm	70 mm
Dimension - B Length inch	1.21 in
Dimension - Outside Diameter inch	0.48 in
Dimension - Length Overall inch	2.75 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 163 • 308
Oxide Inhibitor Type	Penetrox E
UPC	781810014561
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014561

Logistics

Minimum Pack Quantity	1
Pallet Quantity	11600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand