



YDS43R43RS, 2-piece, ACSR Splice,
includes inner and outer sleeves

By Burndy
Catalog # [YDS43R43RS](#)

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	666.6 (24/7) Flamingo kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	.50 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	203 mm
Dimension - Steel Sleeve Length inch	8 in
Dimension - Length Overall inch	8 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 254 • 319
Die Index - Element A	254
Die Index - Element B	319
UPC	781810175903
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810175903
UPC 14 Digit GTIN	00781810175903

Logistics

Minimum Pack Quantity	1
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)