



YDS44, Copper, Single Sleeve Full Tension Splice



By Burndy
Catalog # [YDS44](#)

CU Full Tension Splice, Accommodates Wire: 1000 kcmil Cu
(Hard, Medium, or Soft Drawn), Die Index: 345

Features

- Copper Full Tension Splice
- Single Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	1000 kcmil
-----------------------------	------------

Configuration

Physical Attribute - Number of Crimps Required	10
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-14/25 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	387 mm
Dimension - B Length inch	7.56 in
Dimension - Outside Diameter	2.00 in
Dimension - Length Overall	15.25 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	345
Oxide Inhibitor Type	Penetrox E
UPC	781810014684
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014684

Logistics

Minimum Pack Quantity	1
Pallet Quantity	192
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)