



YDS451AT, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy
Catalog # [YDS451AT](#)

Full tension splice made of aluminum tubing with staked -in cable stop. Designed for all aluminum conductor. ANSI C119.4 Class 1 (Full Tension)

Features

- Aluminum Full Tension Splice
- Staked in Cable Stop

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1272.2(61)kcmil
Conductor - AL Str Size Range	1272.2
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	1113 (54/19) Finch
Conductor - ACSR Str Size Range	1113 (54/19) Finch

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	9-9/53 in



Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	470 mm
Dimension - B Length inch	9.17 in
Dimension - Outside Diameter inch	2.12 in
Dimension - Length Overall inch	18.52 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	422
UPC	781810179338
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810179338
UPC 14 Digit GTIN	00781810179338

Logistics

Minimum Pack Quantity	1
Pallet Quantity	576
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)