



YDS451R49RS, 2-piece, ACSR Splice,  
includes inner and outer sleeves

By Burndy  
Catalog # [YDS451R49RS](#)

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

Conductor

|                                 |                                                                                           |
|---------------------------------|-------------------------------------------------------------------------------------------|
| Conductor - AL Str Size         | 795.5                                                                                     |
| Conductor - AL Str Size Range   | 795.5                                                                                     |
| Conductor Type                  | <ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul> |
| Conductor - ACSR Str Size       | 795 (26/7) Drake                                                                          |
| Conductor - ACSR Str Size Range | 795 (26/7) Drake                                                                          |

Configuration

|                |        |
|----------------|--------|
| Connector Type | Splice |
|----------------|--------|

Dimensions

|                              |                                                                     |
|------------------------------|---------------------------------------------------------------------|
| Package Height               | 0.000 in                                                            |
| Package Weight               | 0.000 lb.                                                           |
| Package Length               | 0.000 in                                                            |
| Package Width                | 0.000 in                                                            |
| Dimension - L Length Overall | 254 mm                                                              |
| Dimension - Length Overall   | 10 in                                                               |
| General                      |                                                                     |
| Plated                       | N                                                                   |
| Trade Name                   | HYSPLICE™                                                           |
| Die Index                    | <ul style="list-style-type: none"><li>• 419</li><li>• 579</li></ul> |
| UPC                          | 781810172032                                                        |
| Prefilled Oxide Inhibitor    | Y                                                                   |
| Material                     | Aluminum                                                            |
| Plating Type                 | Unplated                                                            |
| UPC 14 Digit GTIN            | 00781810172032                                                      |

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalog \[English\]](#)