



YDS45LT, ACSR Full Tension Splice

By Burndy
Catalog # [YDS45LT](#)

Full Tension Splice, 927 kcmil ACSR, 648 Index



Features

- ACSR Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size Range	927.2 (37) kcmil
Conductor - AAAC 6201 Size Range	927.2 (37) kcmil
Conductor - AAAC 6201 Size	927.2 (37) kcmil
Conductor - AAAC 5005 Size	927.2 (37) kcmil
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	10-31/50 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	543 mm
Dimension - B Length inch	10.62 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Length Overall inch	21.36 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	648
UPC	781810014196
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014196

Logistics

Minimum Pack Quantity	1
Pallet Quantity	288
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)