



YDS45R45RS, 2-piece, ACSR Splice,
includes inner and outer sleeves

By Burndy
Catalog # [YDS45R45RS](#)

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	795.5
Conductor - AL Str Size Range	795.5
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	795 (54/7) Condor
Conductor - ACSR Str Size Range	795 (54/7) Condor

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	32.50 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	229 mm
Dimension - Steel Sleeve Length inch	9 in
Dimension - Length Overall inch	9 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 320 • 352
Die Index - Element A	320
Die Index - Element B	352
UPC	781810290019
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810290019

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)