



YDS49R36RS, 2-piece, ACSR Splice,
includes inner and outer sleeves

By Burndy
Catalog # [YDS49R36RS](#)

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1033.5
Conductor - AL Str Size Range	1033.5
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	1033.5 (54/7) Curlew
Conductor - ACSR Str Size Range	1033.5 (54/7) Curlew

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Aluminum Sleeve Length inch	37 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	941 mm
Dimension - Outside Diameter inch	2.12 in
Dimension - Steel Sleeve Length inch	7.857 in
Dimension - Length Overall inch	37.03 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	422
Die Index - Element A	350
Die Index - Element B	422
UPC	781810129371
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810129371

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1776
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)