



YDS49R49RS, 2-piece, ACSR Splice,
includes inner and outside sleeves

By Burndy
Catalog # [YDS49R49RS](#)

Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension)

Features

- 2-Piece ACSR Splice
- Includes inner and outer sleeves

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1033.5
Conductor - AL Str Size Range	1033.5
Conductor Type	• ACSR C Str-Size • AL C Str-Size
Conductor - ACSR Str Size	1033.5 (54/7) Curlew
Conductor - ACSR Str Size Range	1033.5 (54/7) Curlew

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	254 mm
Dimension - Steel Sleeve	10 in
Length inch	
Dimension - Length Overall	10 in
inch	

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 419 • 422
Die Index - Element A	419
Die Index - Element B	422
UPC	781810042434
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810042434

Logistics

Minimum Pack Quantity	1
Pallet Quantity	222
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)



A Hubbell brand