



YDS4CA, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy
Catalog # [YDS4CA](#)

Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension), Die Index:162, 2-5/8 L

Features

- Full-Tension sleeve made of aluminum tubing with staked-in cable stop
- Sizes 1/0 and larger feature a taper for gradual transition of stress
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum Compressed And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	4 (7) AWG
Conductor - ACAR Str Size	4 (7) AWG
Conductor - ACSR Cmpt Size Range	4 AWG
Conductor - ACSR Cmpt Size	4 AWG
Conductor - AAAC 5005 Size Range	48.69 (7) kcmil
Conductor - AAAC 6201 Size Range	48.69 (7) kcmil
Conductor - AAAC 6201 Size	48.69 (7) kcmil
Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor - AAAC 5005 Size	48.69 (7) kcmil
Conductor Type	• ACSR C Str-Size • AL C Str-Size



Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	67 mm
Dimension - Outside Diameter inch	0.4 in
Dimension - B Length inch	1.25 in
Dimension - Inside Diameter inch	0.24 in
Dimension - Length Overall inch	2.62 in

General

Trade Name	HYSPLICE™
Die Index	162
Prefilled Oxide Inhibitor	Y
Plated	N
Color Code	Orange
Sub Brand	HYSPLICE
UPC	781810015377
Type	YDS-A
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810015377

Logistics

Minimum Pack Quantity	1
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand