



YDS4KT, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS4KT](#)



CU Full Tension Splice, Accommodates Wire: 4A COPPERWELD,
Die Index: 163 or 204

Features

- Copper Single Sleeve Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	4A
---------------------------------	----

Configuration

Physical Attribute - Number of Crimps Required	10
Connector Type	Splice

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	160 mm
Dimension - B Length inch	3.03 in
Dimension - Length Overall inch	6.28 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	163 204
UPC	781810820674
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810820674

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7350
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)