



YDS4RLS20, Aluminum Full Tension Splice

By Burndy
Catalog # [YDS4RLS20](#)

Al Compression Full Tension Splice, #4 Smooth Body ACSR
#200 Grade

Features

- Aluminum Compression Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	4 (6/1) Swan AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Length	12.05 in
Dimension - B Length fraction	5-32/33 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	306 mm
Dimension - B Length inch	5.97 in
Dimension - Outside Diameter	0.69 in
Height	0.69 in
Width	0.69 in
Dimension - Inside Diameter	0.31 in
Dimension - Length Overall	12.05 in
inch	
Dimensions	12.05 in x 0.69 in x 0.69 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	245
UPC	621945068636
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00621945068636

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3360
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)



A Hubbell brand