



YDS4W, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS4W](#)

CU Full Tension Splice, Accommodates Wire: #4 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 162

Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Solid Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	RUS
Certification - ETL	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	6 AWG - 3 AWG
Conductor - Copper Solid Size	4 AWG

Configuration

Physical Attribute - Number of	4
Crimps Required	
Connector Type	Splice

Dimensions



Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	65 mm
Dimension - Outside Diameter inch	0.38 in
Dimension - B Length inch	1.15 in
Dimension - Length Overall inch	2.55 in

General

Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Die Index	162
Prefilled Oxide Inhibitor	N
Plated	No
Sub Brand	HYSPLICE
Product Type	Compression
UPC	781810820940
Type	YDS
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810820940

Logistics

Minimum Pack Quantity	1
Pallet Quantity	23200
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)