



YDS4WA, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy
Catalog # [YDS4WA](#)

Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension),Conductor:4(1)

Features

- Aluminum Full Tension Splice
- Staked in Cable Stop

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	4 (7) AWG
Conductor - ACAR Str Size	4 (7) AWG
Conductor - ACSR Cmpt Size Range	4 AWG
Conductor - ACSR Cmpt Size	4 AWG
Conductor - AAAC 5005 Size Range	48.69 (7) kcmil
Conductor - AAAC 6201 Size Range	48.69 (7) kcmil
Conductor - AAAC 6201 Size	48.69 (7) kcmil
Conductor - AL Str Size	4 AWG
Conductor - AAAC 5005 Size	48.69 (7) kcmil
Conductor - AL Str Size Range	4 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------



Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	67 mm
Dimension - B Length inch	1.25 in
Dimension - Outside Diameter	0.39 in
Dimension - Inside Diameter	0.21 in
Dimension - Length Overall	2.62 in

General

Plated	N
Color Code	Orange
Trade Name	HYSPLICE™
Die Index	162
UPC	781810015384
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810015384

Logistics

Minimum Pack Quantity	1
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)