



YDS500H, Full Tension Steel Splice

By Burndy
Catalog # [YDS500H](#)

Full-tension steel splice designed for galvanized steel guy, messenger and "static:" conductors. ANSI C119.4 Class 1 (Full Tension),Die index:293

Features

- Full Tension Steel Splice
- Designed for Galvanized Steel Guy, Messenger and "Static" Conductors


Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Grade	HS
Conductor - Galvanized Steel Str Size	1/2 (19) in
Conductor - Galvanized Steel Str Size Range	1/2 (19) in
Conductor - AL Coated Steel Size Range	1/2 (7) in
Conductor - AL Coated Steel Size	1/2 (7) in
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration



Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	4-22/31 in
Dimension - L Length Overall mm	246 mm
Dimension - B Length inch	4.71 in
Dimension - Outside Diameter inch	0.97 in
Dimension - Length Overall inch	9.69 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	293
UPC	781810016039
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810016039

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1344
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)