



YDS6C, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS6C](#)

CU Full Tension Splice, Accommodates Wire: #6 Cu STR (Hard, Medium, or Soft Drawn), Die Index: 161

Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Stranded Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	6 AWG
-----------------------------	-------

Configuration

Physical Attribute - Number of	1
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
----------------	----------



Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	70 mm
mm	
Dimension - Outside Diameter	0.32 in
inch	
Dimension - B Length fraction	1-13/50 in
Dimension - B Length inch	1.26 in
Dimension - Length Overall	2.77 in
inch	

General

Trade Name	HYSPLICE™
Die Index	161
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	N
Sub Brand	HYSPLICE
UPC	781810821077
Type	YDS - C
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810821077

Logistics

Minimum Pack Quantity	1
Pallet Quantity	46400
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)