



YDS6CA, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy
Catalog # [YDS6CA](#)

Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension),Die Index:161,3 L

Features

- Aluminum Full Tension Splice
- Staked in Cable Stop

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	6 AWG
Conductor - ACSR Cmpt Size	6 AWG
Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor Type	• ACSR C Str-Size • AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.



Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	74 mm
mm	
Dimension - Outside Diameter	0.32 in
inch	
Dimension - Inside Diameter	0.2 in
inch	
Dimension - Length Overall	2.91 in
inch	

General

Plated	N
Trade Name	HYSPLICE™
Die Index	161
UPC	781810015391
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810015391

Logistics

Minimum Pack Quantity	1
Pallet Quantity	46400
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)