



YDS6KT, Copper Full Tension Splice

By Burndy
Catalog # [YDS6KT](#)

CU Full Tension Splice, Accommodates Wire: 6A COPPERWELD, Die Index: 162 or 203

Features

- Copper Full Tension Compression Splice

Application

For Copperweld-Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	6 A AWG
---------------------------------	---------

Configuration

Physical Attribute - Number of	10
Crimps Required	
Connector Type	Splice

Dimensions

Dimension - Pin Diameter inch	0.43 in
Package Height	0.000 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	154 mm
Dimension - B Length inch	2.83 in
Dimension - Length Overall inch	6.06 in

General

Plated	No
Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Sub Brand	HYSPLICE
Die Index	162 203
Product Type	Compression
UPC	781810014578
Type	YDS-KT, High Voltage
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014578

Logistics

Minimum Pack Quantity	100
Pallet Quantity	11100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)