



YDS6RLS20CG1, Aluminum, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS6RLS20CG1](#)

Single sleeve aluminum UNISPLICE; Full tension aluminum and ACSR applications; prefilled with PENETROX joint compound



Features

- Aluminum Single Sleeve Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	5-22/25 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	305 mm
Dimension - B Length inch	5.88 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Inside Diameter inch	0.28 in
Dimension - Length Overall inch	12 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	165
UPC	621945068759
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00621945068759

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2016
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)