



YDS6W, Copper Full Tension Splice

By Burndy
Catalog # [YDS6W](#)



CU Full Tension Splice, Accommodates Wire: #6 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 161

Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Solid Copper Conductors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	6 AWG
-------------------------------	-------

Configuration

Physical Attribute - Number of	4
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	67 mm
Dimension - B Length inch	1.27 in
Dimension - Outside Diameter inch	0.32 in
Dimension - Length Overall inch	2.62 in

General

Plated	No
Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Sub Brand	HYSPLICE
Die Index	161
Product Type	Compression
UPC	781810820667
Type	YDS
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810820667

Logistics

Minimum Pack Quantity	1
Pallet Quantity	46400
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)