



YDS6WA, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy
Catalog # [YDS6WA](#)

Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension)

Features

- Aluminum Full Tension Splice
- Staked in Cable Stop

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	6 AWG
Conductor - ACSR Cmpt Size	6 AWG
Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-2/5 in
Package Weight	0.000 lb.



Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	74 mm
Dimension - B Length inch	1.4 in
Dimension - Outside Diameter inch	0.33 in
Dimension - Inside Diameter inch	0.18 in
Dimension - Length Overall inch	2.91 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	161
UPC	781810015414
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810015414

Logistics

Minimum Pack Quantity	1
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)