

YDS75. Copper Full Tension Splice

By Burndy
Catalog # [YDS75](#)



CU Full Tension Splice, Accommodates Wire: 1/0 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 165

Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Solid Copper Conductors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	1/0 AWG
-------------------------------	---------

Configuration

Physical Attribute - Number of	6
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	151 mm
Dimension - B Length inch	2.84 in
Dimension - Outside Diameter inch	0.61 in
Dimension - Length Overall inch	5.93 in

General

Plated	No
Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Sub Brand	HYSPLICE
Die Index	• 165 • 287
Product Type	Compression
Oxide Inhibitor Type	Penetrox E
UPC	781810564806
Type	YDS
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810564806

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4900
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)