



YDS76, Copper Full Tension Splice

By Burndy
Catalog # [YDS76](#)

CU Full Tension Splice, Accommodates Wire: 2/0 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 166



Features

- Copper Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Solid Copper Conductors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	2/0 AWG
-------------------------------	---------

Configuration

Physical Attribute - Number of	6
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	157 mm
mm	
Dimension - B Length inch	2.97 in
Dimension - Outside Diameter	0.68 in
inch	
Dimension - Length Overall	6.19 in
inch	

General

Plated	N
Trade Name	HYSPLICE™
Sub Brand	HYSPLICE
Die Index	• 166 • 206
Oxide Inhibitor Type	Penetrox E
UPC	781810014691
Type	YDS
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014691

Logistics

Minimum Pack Quantity	25
Pallet Quantity	3675
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)