




YDS77, Copper Full Tension Splice

By Burndy
Catalog # [YDS77](#)



CU Full Tension Splice, Accommodates Wire: 3/0 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 207

Features

- Copper Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	3/0 AWG
-------------------------------	---------

Configuration

Physical Attribute - Number of	7
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	188 mm
Dimension - B Length inch	3.51 in
Dimension - Outside Diameter	0.76 in
Dimension - Length Overall	7.39 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	207
Oxide Inhibitor Type	Penetrox E
UPC	781810014134
Prefilled Oxide Inhibitor	Y
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014134

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1225
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)